

## Detailed Specifications

<b>BDL600IR optics</b>	
Glass display	Fused silica glass coated with indium-tin oxide conductive layer and P31 phosphor (ZnS:Ag:Cu-green, 525 nm wavelength)
Angle of acceptance	93° from the sample at a distance of 50 mm
Retarding Field Analyzer	Concentric assembly of hemispherical grids
Working distance from sample	15 mm
Grid material	Gold-coated St-Steel wire mesh (100 mesh, 81% transparency)
Energy resolution	0.2% -0.5% at low modulation voltage
Monitoring	6" standard viewport
Linear motion	Up to 150 mm retraction from the sample; linear ball bearing and acme thread with all spring electrical connections
Integral shutter	Manual shutter driven by a rotary feedthrough
Magnetic shielding	Mu metal cylinder with front cover for maximum attenuation
Assembly	Extreme high vacuum compatibility with stainless steel, high alumina and Au-plated copper alloy materials
Mounting	CF6" (DN100CF) double-sided conflat flange w. sample distance 145 mm – 500mm
Bakeability	Under vacuum, 250°C maximum

<b>Integral miniature electron gun</b>	
Beam energy	LEED: 0-750 eV AES: 0-3000 eV
Beam current	LEED: 2 $\mu$ A at 100 eV and 0.5 mm beam size AES: up to 100 $\mu$ A at 3 keV
Beam size	From 1 mm to 250 $\mu$ m-adjusted by wehnelt potential
Electron source	Tungsten 2% thoriated filament (standard) or single crystal LaB <sub>6</sub> filament (optional)
Energy spread	0.45 eV (thoriated-tungsten filament)
Overall size	10 mm lens diameter and 80 mm length